REDMETERS










KEY ADVANTAGES


- + Simple, Non-Nuclear Solution
- + Low Total Cost of Ownership
- + Remote Support and Updates

- + Real Time Measurement Readings
- + Simple to Install and Maintain
- + Highly Accurate and Repeatable



ANATOMY | MECHANICAL

Proprietary Cartridge








PRINCIPLE OF OPERATION

- All media passes through a flexible inline cartridge.
- The change in deflection of the cartridge is read by a highly sensitive laser. In addition, temperate and pressure are recorded.
- As the weight change is measured within a fixed volume, the density is calculated using data recorded by the sensors and computed using our proprietary machine learning algorithms.
- The calculated readings are displayed and graphed on screen. This data can be output in real time as well as exported for archival and analysis.







ANATOMY | SOFTWARE

CORE FEATURES

- + Selectable Display Options
- + PIN-Secured Configuration & Calibration Menu
- + Remote Interface (HMI)
- + Remote Support & Upgrades
- + 4-20 mA Output*
- + Modbus TCP
- + RS485 (Modbus)
- + Optional HART Output







EASY TO USE INTERFACE

DISPLAY VALUES

- + Density or Specific Gravity
- + Solids Component Content
- + Media Pressure
- + *Flow Rate
- + *Mass Flow
- + *Solids Accumulator
- + *Flow Rate vs SG
 with Configurable Optimized Range Setting

(* requires optional flow meter)







ONE BUTTON CONFIGURATION









INSTALLATION CONSIDERATIONS


- 1 Pipe Opening and Flanging
- 2 Flange Specifications
- 3 Secure Base for Pipe Supports
- 4 Available Power Supply
- 5 Available Connectivity







INSTALLATION EXAMPLES







EASY TO INSTALL

Bolt in installation







MOBILE BASE

Density meter + flow meter on a single, mobile base.








KEY ADVANTAGES

- + Simple, Non-Nuclear Solution
- + Low Total Cost of Ownership
- + Remote Support and Updates

- + Real Time Measurement Readings
- + Simple to Install and Maintain
- + Highly Accurate and Repeatable



REDMETERS

